

Optics Materials and Applications

Flats, spheres, and aspheres

OVERVIEW

Entegris' POCO Materials are the material of choice for performance benefits beyond what beryllium, aluminum, glass, and other types of silicon carbide can offer. Our SUPERSiC® (SiC) silicon carbide has high stiffness and strength, excellent thermal properties, and stability in cryogenic environments, without the health concerns of beryllium. These superior characteristics make the SUPERSiC material an ideal selection for industrial, space-based, and airborne/ground electro-optical applications.

Reflective optics manufactured from SUPERSiC silicon carbide material are uniquely suited to offer high optical quality mirrors for demanding applications. Substrates made from this material are the preform foundation onto which chemical vapor deposited silicon carbide, or optical-grade silicon coatings are applied. Application of either coating provides a ready-made substrate for subsequent polishing and reflectance coat finishing.


SHAPES

Our unique chemical vapor conversion (CVC) process provides innovators the ability to design complex shapes and contours that would be expensive and difficult to manufacture by other methods. Conventional lathe and mill machining equipment and tools are used to produce a graphite preform to near-net shape. Our process allows the freedom to create complex shapes with no more difficulty than would be experienced using aluminum. The CVC process completes the transformation from graphite to 100% silicon carbide.

Flats, spheres, aspheres, or off-axis aspheric contours are easily manufactured with the SUPERSiC silicon carbide process. Shape-making ability is further complemented through conversion bonding or reaction-bonded silicon carbide (RBSC) technologies. Structural and optical designs may incorporate closed-cell and back plate features for added stiffness and weight reduction, while maintaining the structural integrity of a monolith.



Silicon clad spherical mirror



Lightweight flat silicon carbide mirrors



Galvo silicon carbide scanning mirrors

COATINGS

Polishing

SUPERSiC silicon carbide contains about 18% residual porosity, providing a substrate core that is inherently lightweight. Applying an encapsulating or selectively placed coating completes the substrate's preparation. We offers three coatings as a polishing surface: chemical vapor deposition (CVD) SiC, non-crystalline silicon, and crystalline silicon. These coatings may be conventionally polished or, in the case of silicon, single-point diamond turned. All three options offer distinct advantages in performance, cost, and lead time.

APPLICATIONS

Scan Mirrors

Precise dynamic response from an optic within a scanning system is paramount to its successful operation. Scan mirrors made from SUPERSiC grade materials are lightweight but exceptionally stiff to provide the characteristics desired under rapid motion conditions. Designs may use open- or closed-back structures for improved rigidity and stability. Laser-based applications where energy dissipation is a concern also benefit from SUPERSiC silicon carbide's excellent thermal properties.

Lithography

Precision dynamic response is not limited to optic alone. Lithography applications benefit from the mechanical performance of SUPERSiC material as well. SUPERSiC silicon carbide provides considerable mechanical stiffness through a wide range of temperatures. Applying a CVD SiC coating on SUPERSiC silicon carbide components ensures protection against particulate contamination, effectively sealing the parts and making them lightweight, stiff and clean – all factors highly desired for lithography processing.

Telescope – Structures and Mirrors

Assembling a telescope with metering structures and optics made of the same material is the "Holy Grail" of material configurations. Using SUPERSiC materials for both structures and mirrors is a major advance towards optimal performance by eliminating errors induced from mismatched properties. Space-based applications, in particular, benefit considerably from

the low coefficient of thermal expansion and high stiffness of our SUPERSiC materials. The suite of options available – increased elastic modulus from SUPERSiC-Si grade, CVD SiC coatings, Si claddings, reflectance coatings, and others – provides multiple selections for any design project.

SUPERSiC MATERIALS

Our unique conversion process produces the highest quality silicon carbide products available on the market today. This process starts with graphite material specially designed and manufactured for use as the precursor in the conversion process.

Near-net shaped parts are machined in graphite, purified, and subjected to a proprietary conversion process that substitutes pure silicon atoms for carbon atoms. During conversion, we have the ability to fuse parts so they enter the furnace as an assembly of individual pieces and exit as a monolithic unit, with properties indistinguishable from those of a part originally made from one piece. This is done without the use of adhesives or other bonding agents. This conversion bonding process enables the creation of extremely complex, lightweight structures for aerospace optics such as spaceflight worthy, closed-back, off-axis, or aspherical mirrors for satellite systems. These material and process advantages have placed us at the forefront of silicon carbide component development.

SUPERSiC

SUPERSiC silicon carbide is our base SiC converted graphite.

SUPERSiC-3C

SUPERSiC-3C grade is SUPERSiC silicon carbide that has been coated with a 75 μm CVD SiC coating, which encapsulates the substrate and seals the surface. This material is ideal for low-cost optics and structures.

SUPERSiC-Si

SUPERSiC-Si grade is SUPERSiC silicon carbide that has been infiltrated with high-purity silicon, giving it improved mechanical properties over SUPERSiC material. This grade is ideal for CVD SiC coating or silicon cladding.

SUPERSiC-Si-3C

SUPERSiC-Si-3C grade is SUPERSiC silicon carbide that has been infiltrated with silicon and then coated with a 75 µm CVD SiC coating, sealing the porosity. This material is ideal for space-based optics and structures.

SUPERSiC-Si-8C

SUPERSiC-Si-8C grade is SUPERSiC silicon carbide that has been infiltrated with silicon and then coated with a 200 µm CVD SiC coating. This material is ideal for large optics and lithography components.

SUPERSiC-Si-4S

SUPERSiC-Si-4S grade is SUPERSiC silicon carbide that has been infiltrated with silicon and then selectively clad with a 100 µm silicon cladding. This material is ideal for single-point diamond turning (SPDT), for reduced lead time and total cost.

SUPERSiC-SP

SUPERSiC-SP grade is the newest grade in our family of silicon carbide materials. This product improves on the mechanical properties of SUPERSiC-Si material by changing the densification material from silicon to silicon carbide.* The result is a material that is stronger in flex and tensile load. Further, the monolithic material ensures an even more uniform response to thermal loading.

**Some trace amounts of free silicon will remain.*

TYPICAL MATERIAL PROPERTIES

PROPERTY	SUPERSiC	SUPERSiC-3C (-3CX)	SUPERSiC-Si (-4S)	SUPERSiC-Si-3C (-8C)	SUPERSiC-SP
Apparent density	3.13 g/cm ³ (0.113 lb/in ³)	3.15 g/cm ³ (0.114 lb/in ³)	3.01 g/cm ³ (0.109 lb/in ³)	3.03 g/cm ³ (0.110 lb/in ³)	3.04 g/cm ³ (0.110 lb/in ³)
Bulk density	2.53 g/cm ³ (0.092 lb/in ³)	2.55 g/cm ³ (0.092 lb/in ³)	2.93 g/cm ³ (0.106 lb/in ³)	2.95 g/cm ³ (0.107 lb/in ³)	3.00 g/cm ³ (0.109 lb/in ³)
Total porosity: % of volume	20%	20% [†]	4%	4% [†]	5%
Open porosity: % of total	19%	0% ^{††}	1%	0% ^{††}	1%
Total impurity level	<10 ppm	<10 ppm	<10 ppm	<10 ppm	<10 ppm
Flexural strength	155 MPa (22,400 psi)	155 MPa (22,400 psi)	192 MPa (27,900 psi)	192 MPa (27,900 psi)	220 MPa (31,900 psi)
Tensile strength	129 MPa (18,700 psi)	129 MPa (18,700 psi)	124 MPa (17,940 psi)	124 MPa (17,940 psi)	162 MPa (23,510 psi)
Elastic modulus	217 GPa (31 10 ⁶ psi)	217 GPa (31 10 ⁶ psi)	331 GPa (48 10 ⁶ psi)	331 GPa (48 10 ⁶ psi)	373 GPa (54 10 ⁶ psi)
Specific stiffness	86 kN.m/g	85 kN.m/g	113 kN.m/g	112 kN.m/g	124 kN.m/g
Poisson's ratio	0.17	0.17	0.17	0.17	0.17

PROPERTY	SUPERSiC	SUPERSiC-3C (-3CX)	SUPERSiC-Si (-4S)	SUPERSiC-Si-3C (-8C)	SUPERSiC-SP
Dynamic shear modulus	97 GPa (14 10 ⁶ psi)	97 GPa (14 10 ⁶ psi)	138 GPa (20 10 ⁶ psi)	138 GPa (20 10 ⁶ psi)	159 GPa (23 10 ⁶ psi)
Fracture toughness	2.44 MPa.m ^{0.5}	2.44 MPa.m ^{0.5}	3.78 MPa.m ^{0.5}	3.78 MPa.m ^{0.5}	N/A
Hardness knoop	1992 kg/mm ²	N/A	1643 kg/mm ²	N/A	N/A
Thermal diffusivity	100 mm ² /s	100 mm ² /s	115 mm ² /s	115 mm ² /s	111 mm ² /s
Thermal conductivity	170 W/(cm·K) (98 Btu/hr/ft ² °F)	170 W/(cm·K) (98 Btu/hr/ft ² °F)	220 W/(cm·K) (127 Btu/hr/ft ² °F)	220 W/(cm·K) (127 Btu/hr/ft ² °F)	224 W/(cm·K) (129 Btu/hr/ft ² °F)
Electrical resistivity	0.009 Ω-cm (3700 μΩ-in)	N/A	0.010 Ω-cm (4000 μΩ-in)	N/A	0.008 Ω-cm (3280 μΩ-in)
Instantaneous coefficient of thermal expansion at RT	2.4 10 ⁻⁶ /K (1.3 10 ⁻⁶ /°F)	2.4 10 ⁻⁶ /K (1.3 10 ⁻⁶ /°F)	2.4 10 ⁻⁶ /K (1.3 10 ⁻⁶ /°F)	2.4 10 ⁻⁶ /K (1.3 10 ⁻⁶ /°F)	2.4 10 ⁻⁶ /K (1.3 10 ⁻⁶ /°F)

^tPorosity is sealed under the dense coating; porosity is not exposed to the process.

^{††}Porosity sealed off by CVD SiC coating.

FOR MORE INFORMATION

Please call our Customer Service Center today to learn what our premium graphite and silicon carbide solutions can do for you. Visit poco.entegris.com/contact-us for the location nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Poco Graphite's Terms and Conditions of Sale. To view and print this information, visit poco.entegris.com/terms-and-conditions.



300 Old Greenwood Road
Decatur, Texas 76234
USA

Customer Service
Tel +1 940 627 2121
Fax +1 940 393 8366

Entegris® and the Entegris Rings Design® are trademarks of Entegris, Inc., and POCO® and other product names are trademarks of Poco Graphite, Inc., as listed on entegris.com/trademarks. All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2010-2020 Entegris, Inc. | All rights reserved. | Printed in the USA | 6207-10995TAN-0320